

JETCHISEL Model **JT-10**

Super lightweight and palm-sized

- Remove weld slag, rust and paint
- Easily change needles without any tools
- 1.6 mm dia. Needles for detailed work



**First
in the series!**

Weight
500 g
(With hose)

Stainless
steel needles
are also available
as option



Equipped with
a flow control lever



① Push the bending portion of the safety band and loosen the lock ring, then take out the needle supporter.

② Insert the new needles into the needle supporter.

③ Repeat the previous steps in reverse to assemble.



Palm-sized and easy to grip design



Remove paint



Deburr die casting



Remove weld slag

Model		JT-10
Air Pressure	MPa (bar, PSI)	0.6 (6, 85)
Air Consumption (No-load)	m ³ /min (CFM)	0.10 (3.6)
Strokes per Minute	min ⁻¹ (SPM)	5500 (5500)
Number of needles used	pcs	7
Standard length of needle	mm (inch)	120 (4.72)
Mass (Weight)	kg (lbs)	0.5 (1.1) with air hose
Accessories Included		• 7 pieces of 1.6 mm x 120 mm Steel Needles (Installed) • 7 pieces of 1.6 mm x 120 mm Steel Needles • Air Hose E Ass'y

Technical drawing of the 1000 Series Needle. The drawing shows a side view of the needle assembly with the following dimensions and callouts:


- Overall length: 161.3 [6.35"]
- Needle length: 69 [2.72"]
- Stroke length: 6.5 [0.256"]
- Needle diameter: 24.5 [31/32"] OD
- Needle tip diameter: 24.5 [31/32"] OD
- Needle body diameter: 21.5 [27/32"] OD
- Needle thread: Rc 1/8
- Needle material: 7 pieces of 1.6 mm x 120 mm Needles [1/16" x 4.72"]

(Unit: mm [inch])

Slim model
AJC-16



Heavy-duty model
JEX-28




Reduced vibration model
JEX-20



Reduced vibration model
JEX-2800A




Electric type
EJC-32A



1.6 mm x 120 mm Needles



(Steel)



(Stainless Steel)

- 50 pcs./set (PN: TB10658)
- 25 pcs./set (PN: TB11516)
- 50 pcs./set (PN: TB10659)

Web www.nitto-kohki.co.jp/e/

9-4, Nakaikogami 2-chome, Ohta-ku, Tokyo 146-8555, Japan
Tel : +81-3-3755-1111 Fax : +81-3-3753-8791
E-mail : overseas@nitto-kohki.co.jp



ISO9001
JQA-2025
ISO14001
JQA-EM4057
H Q / B & D Lab

DISTRIBUTED BY